

표준 XLCR 제품번호

| 제품번호 | 제품명 | 동력 P2 (kW) |
|----------|--|------------|
| 92805823 | CR95-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92642652 | CR95-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92652090 | CR95-3-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92642664 | CR95-4-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92805825 | CR95-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805827 | CR95-5-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805829 | CR95-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805852 | CR95-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805855 | CR95-3-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805859 | CR95-4-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805861 | CR95-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805862 | CR95-5-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805893 | CR125-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92805895 | CR125-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92805896 | CR125-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92628876 | CR125-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805898 | CR125-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805899 | CR125-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805910 | CR125-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805911 | CR125-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805944 | CR155-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92690127 | CR155-2-2 A-F-A-E-HQQE 380D/660Y 60 Hz | 37 |
| 92805945 | CR155-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92805946 | CR155-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92628874 | CR155-3-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805947 | CR155-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805948 | CR155-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805949 | CR155-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805950 | CR155-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805951 | CR155-3-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805982 | CR185-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92805983 | CR185-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92643878 | CR185-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92805984 | CR185-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92627838 | CR185-3-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92627873 | CR185-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92805985 | CR185-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92805986 | CR185-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92805987 | CR185-5-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92805988 | CR185-5 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92805989 | CR185-6-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92805990 | CR185-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805991 | CR185-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805992 | CR185-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92805993 | CR185-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |

표준 XLCR 제품번호

| 제품번호 | 제품명 | 동력 P2 (kW) |
|----------|--|------------|
| 92805994 | CR185-3-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92805995 | CR185-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92805996 | CR185-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92805997 | CR185-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92805998 | CR185-5-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806010 | CR185-5 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806011 | CR185-6-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806033 | CR215-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92806035 | CR215-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92806039 | CR215-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92806040 | CR215-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92806041 | CR215-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806042 | CR215-3-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806043 | CR215-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806045 | CR215-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806046 | CR215-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806047 | CR215-4-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806048 | CR215-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92806050 | CR215-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92806052 | CR215-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92806053 | CR215-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |
| 92806054 | CR215-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806055 | CR215-3-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806056 | CR215-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806057 | CR215-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806058 | CR215-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806059 | CR215-4-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806091 | CR255-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92806092 | CR255-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92806094 | CR255-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806095 | CR255-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806097 | CR255-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806098 | CR255-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806101 | CR255-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806102 | CR255-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806103 | CR255-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92806104 | CR255-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92806105 | CR255-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806107 | CR255-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806108 | CR255-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806109 | CR255-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806110 | CR255-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806111 | CR255-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |

표준 XLCR 제품번호

| 제품번호 | 제품명 | 동력 P2 (kW) |
|----------|---|------------|
| 92805863 | CRN95-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92805865 | CRN95-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92665626 | CRN95-3-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92747028 | CRN95-4-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92805866 | CRN95-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805867 | CRN95-5-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805882 | CRN95-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805883 | CRN95-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805885 | CRN95-3-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805886 | CRN95-4-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805887 | CRN95-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805889 | CRN95-5-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92750760 | CRN125-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92750788 | CRN125-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92805912 | CRN125-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92805913 | CRN125-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92805914 | CRN125-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92805915 | CRN125-5-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92805916 | CRN125-5 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92805917 | CRN125-6 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92805922 | CRN125-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805923 | CRN125-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805925 | CRN125-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805926 | CRN125-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805927 | CRN125-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92805928 | CRN125-5-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |
| 92805929 | CRN125-5 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92805940 | CRN125-6 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92805952 | CRN155-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 30 |
| 92629184 | CRN155-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92805953 | CRN155-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92805954 | CRN155-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92628875 | CRN155-3-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92646804 | CRN155-3-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92627876 | CRN155-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92805955 | CRN155-4-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92805956 | CRN155-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92805957 | CRN155-5-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92805964 | CRN155-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 30 |
| 92805965 | CRN155-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92805966 | CRN155-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92805967 | CRN155-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805970 | CRN155-3-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92805971 | CRN155-3-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92805972 | CRN155-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |

표준 XLCR 제품번호

| 제품번호 | 제품명 | 동력 P2 (kW) |
|----------|---|------------|
| 92805973 | CRN155-4-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |
| 92805974 | CRN155-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92805975 | CRN155-5-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806012 | CRN185-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 37 |
| 92806013 | CRN185-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92659218 | CRN185-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92806014 | CRN185-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92806015 | CRN185-3-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806016 | CRN185-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806017 | CRN185-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806018 | CRN185-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806019 | CRN185-5-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806020 | CRN185-5 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806021 | CRN185-6-4 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806022 | CRN185-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 37 |
| 92806023 | CRN185-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92806024 | CRN185-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92806025 | CRN185-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |
| 92806026 | CRN185-3-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806027 | CRN185-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806028 | CRN185-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806029 | CRN185-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806030 | CRN185-5-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806031 | CRN185-5 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806032 | CRN185-6-4 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806060 | CRN215-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 45 |
| 92806062 | CRN215-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92806063 | CRN215-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92706585 | CRN215-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 90 |
| 92806064 | CRN215-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806065 | CRN215-3-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806066 | CRN215-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806067 | CRN215-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806068 | CRN215-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806069 | CRN215-4-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806070 | CRN215-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 45 |
| 92806071 | CRN215-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92806072 | CRN215-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92806073 | CRN215-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 90 |
| 92806074 | CRN215-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806076 | CRN215-3-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806077 | CRN215-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806078 | CRN215-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806079 | CRN215-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806090 | CRN215-4-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |

표준 XLCR 제품번호

| 제품번호 | 제품명 | 동력 P2 (kW) |
|----------|---|------------|
| 92806112 | CRN255-1-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 55 |
| 92806114 | CRN255-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 75 |
| 92806115 | CRN255-2-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806116 | CRN255-2-1 A-F-A-E-HQQE 380D/660Y 60 HZ | 110 |
| 92806118 | CRN255-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 132 |
| 92806119 | CRN255-3-2 A-F-A-E-HQQE 380D/660Y 60 HZ | 160 |
| 92806120 | CRN255-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806121 | CRN255-4-3 A-F-A-E-HQQE 380D/660Y 60 HZ | 200 |
| 92806122 | CRN255-1-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 55 |
| 92806123 | CRN255-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 75 |
| 92806124 | CRN255-2-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806125 | CRN255-2-1 A-F-A-V-HQQV 380D/660Y 60 HZ | 110 |
| 92806126 | CRN255-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 132 |
| 92806127 | CRN255-3-2 A-F-A-V-HQQV 380D/660Y 60 HZ | 160 |
| 92806128 | CRN255-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |
| 92806129 | CRN255-4-3 A-F-A-V-HQQV 380D/660Y 60 HZ | 200 |